

# ACUROS® CQD® 1280 GigE eSWIR Camera

## ACUROS-1280-GigE-002

The ACUROS CQD extended SWIR (eSWIR) cameras have sensitivity from 400 nm to 2000 nm. This novel, wide bandwidth capability opens up new applications for chemical sensing, surveillance imaging, plastic sorting, and more. Acuros eSWIR cameras have unmatched SNR without the need for expensive cooling systems.

### SPECIFICATIONS

Table 1. ELECTRO-OPTICAL SPECIFICATIONS

| Parameter                         | Value/Description                           |
|-----------------------------------|---------------------------------------------|
| Sensor                            | ACUROS CQD sensor                           |
| Temperature Stabilization         | Single-stage thermo-electric cooler         |
| Sensor Array Format               | 1280 x 1024                                 |
| Resolution                        | 1.31 MP (megapixel)                         |
| Spectral Band                     | 400–2000 nm                                 |
| Array Size                        | 19.2 mm x 15.4 mm,<br>24.6 mm diagonal      |
| Pixel Pitch                       | 15 $\mu$ m x 15 $\mu$ m                     |
| Max Frame Rate at Full Resolution | 88 fps (8 bit),<br>45 fps (10, 12, 14 bit)  |
| Pixel Operability                 | 99.9% typical, 99.75% min                   |
| Bit Depth                         | 8, 10, 12, 14 bit selectable                |
| Integration Type                  | Snapshot global shutter                     |
| Trigger                           | External TTL                                |
| Integration Time                  | 100 $\mu$ s to 4 s                          |
| Dynamic Range                     | 65 dB typical                               |
| Windowing                         | Array centered                              |
| Windowing Frame Rate              | Scales inversely to window size             |
| Binning Arrays                    | 2 x 2, 4 x 4                                |
| Non-uniformity Correction         | 2-point non-uniformity correction           |
| Temporal Dark Noise               | 80/70/65 e <sup>-</sup> typical             |
| Detectivity                       | See typical detectivity curve<br>(Figure 4) |



### ORDERING INFORMATION

| Part Number          |
|----------------------|
| ACUROS-1280-GigE-002 |

### Features

- HD Resolution
- TEC Cooling
- Low Noise
- Fast Frame Rate
- Visible-eSWIR
- GigE Vision

### Applications

- Hydrocarbon Detection
- Chemical Sensing
- Medical Imaging
- Plastic Sorting
- Hyperspectral
- High Resolution
- Thermal Imaging
- Surveillance
- Machine Vision
- Silicon Inspection
- Instrumentation

## ACUROS-1280-GigE-002

**Table 2. ENVIRONMENTAL & POWER SPECIFICATIONS, TYPICAL PERFORMANCE**

| Parameter                  | Value/Description                  |
|----------------------------|------------------------------------|
| Operating Case Temperature | –20 °C to +55 °C                   |
| Power Consumption          | 6.5–12 W depending on TEC settings |
| Power Supply Voltage       | 6–16 V dc. POE not supported       |
| Regulatory Compliance      | CE mark                            |

**Table 3. MECHANICAL SPECIFICATIONS**

| Parameter                 | Value/Description                               |
|---------------------------|-------------------------------------------------|
| Dimensions Excluding Lens | 6.1 x 6.1 x 10.9 cm (C-mount)                   |
| Weight Excluding Lens     | 600 grams with C-mount adapter, 594 g (F-mount) |
| Lens Mounts               | C, F, M42 (C-mount flange-back distance)        |
| Power Connector           | Hirose 12-pin, HR10A-10R-12PB (71)              |
| Trigger Connector         | BNC                                             |

**Table 4. SOFTWARE AND USER INTERFACE**

| Parameter                | Value/Description                                     |
|--------------------------|-------------------------------------------------------|
| Software Development Kit | Windows GUI & Pleora eBUS SDK (Linux, Windows, macOS) |
| GenICam Compliance       | Yes                                                   |
| Interface                | GigE Vision                                           |




**Figure 1. C-mount, F-mount, and M-42 Lens Mounts**




**Figure 2. GigE Vision Interface**

## ACUROS-1280-GigE-002



**Figure 3. ACUROS CQD SWIR Camera Images**




**Figure 4. Typical Detectivity Performance**

ACUROS, CQD and SWIR VISION SYSTEMS are registered trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. All other brand names and product names appearing in this document are registered trademarks or trademarks of their respective holders.

**CMOD 103.43x61.00x61.00**  
**CASE 810AA**  
**ISSUE O**

DATE 16 OCT 2024



**NOTES:**

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M. 2018.
2. CONTROLLING DIMENSION: MILLIMETER
3. POWER INDICATOR
4. HIROSE 12 PIN CONNECTOR
5. GigE CONNECTOR
6. M42 MOUNT DEPTH  $\nabla$  9.8
7. M3X0.5 DEPTH  $\nabla$  8.5
8. 1/4-20 UNC DEPTH  $\nabla$  5.08

|                         |                                |                                                                                                                                                                                     |
|-------------------------|--------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98AON65003H</b>             | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>CMOD 103.43x61.00x61.00</b> | <b>PAGE 1 OF 1</b>                                                                                                                                                                  |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)